








NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0 $\pm$ 0.4
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 125VAC, 10A, 250VAC UL&CUL APPROVED
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: -20°C to 85°C
9. 12V RED LED
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT.

SWITCH FUNCTION		
POS. 1	POS. 2	
ON	OFF	
2-1	OPEN	

TITLE			
RR3112BLKBLKREDEF4			
SCALE			
2:1			
DATE			
12/01/2006			
DR			
TN			
DWG			
F130459			
REV			
A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[RR3112LBLKBLKREDEF4](#)