


- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
 3. TERMINAL NUMBERS FOR REF. ONLY
 4. CONTACT RATING: 0.1A @ 30VDC
 5. CONTACT RESISTANCE: 50m OHMS MAX.
 6. TRAVEL: FULL = 2.5± 0.3
 7. OPERATING FORCE: 250± 100gf
 8. ELECTRICAL LIFE: 10,000 CYCLES
 9. ▲DENOTES CRITICAL PARAMETER
 10. CONTACT MATERIAL: SILVER
 11. INSULATING TEMPERATURE: -20c TO +70c
 12. INSULATION RESISTANCE: 100M OHMS MIN
 13. LED COLOR: RED
 14. 2002/95/EC (ROHS) COMPLIANT AND HALOGEN FREE



▲ LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	2.0-2.4
LUMINOUS INTENSITY	MCD	120

 E-SWITCH™				
TITLE TL2205OABPRA				
SCALE	2:1	DATE	1/20/2010	DR rc
			DWG	B401001
			REV	B

14: 2004/05/EC (NOTES) COMPLIANT AND TOLERANCE FREE				
B	19554	DIM CHANGES & UPDATE	12/30/10	BGL
A	18806	New-Release	1/20/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2205OABPRA](#)