







NOTE:
CONTACTS & BRACKET
CROPPED FOR CLARITY



RECOMMEND P.C.B. LAYOUT




CIRCUIT: SPDT

CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
<DN>	OFF	<DN>	
2-3	OPEN	2-1	

()=Momentary



- NOTES:
1. ALL DIMENSIONS IN MM
 2. TERM NUMBERS FOR REFERENCE ONLY
 3. RATING: 5A @250VAC OR 28VDC
 4. TOLERANCES: XX±0.4
X.XX±0.25

E-SWITCH®

C	15420	CHANGES NOTED WERE 318,2,36	10/20/05	PH
B		REVISED & REDRAWN	7/23/97	
REV.	ECN	DESCRIPTION	DATE	CHK

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE				
300 SP-4 J1 M6 Q E				
SCALE	DATE	DR	DWG	REV
2:1	6/6/96	MM	T314000	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300SP4J1M6QE](#)