





PC MOUNTING






▲ CIRCUIT: OFF - (ON)

NOTES:



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4

X.XX=±0.25

3. RATING: 12VDC, 50mA MAX.
4. CONTACT RESISTANCE: 500mΩ MAX.
5. INSULATION RESISTANCE: 100VDC, 100MΩ MIN.
6. TRAVEL: 0.25 mm
7. OPERATING FORCE: 160 +75/-30gf
8. OPERATING TEMPERATURE: -20°C TO 70°C
9. OPERATING LIFE: 30,000 CYCLES.
10. PACKAGING: TAPE & REEL, 3000 PIECES PER REEL
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT
13. PLASTIC MATERIALS MEET OR EXCEED UL94-V0



ISOMETRIC



LED Specifications	Units	BLUE	BLUE
Forward Current	mA	30	30
Forward Voltage	V	3.5-3.8	3.5-3.8
Luminous Intensity@20mA	mcd	45	45



E-SWITCH®



TITLE TL3200AF160BBQ

SCALE 8:1

DATE 10/19/2010

DR BLR

DWG B200108

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	19366	ADD NOTE 13	10/19/10	BLR
A	19114	RELEASED FOR PRODUCTION	6/9/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3200AF160BBQ](#)