





NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C TO 85°C
6. CONTACT RESISTANCE: 30mΩ MAX. INITIAL
7. 2002/95/EC (ROHS) COMPLIANT
8. ▲ DENOTES CRITICAL PARAMETER
9. CONTACT RATING: UL 16A 125VAC, 12A 250VAC, 1HP/250VAC



C	21089	9.50 WAS 12.10	4/2/13	EBP					
B	21034	ADD TOLERANCE TO ACTUATOR POS	2/14/13	EBP					
A	20592	New Release	5/7/12	rc	TITLE PP1 DB7 2A2				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1:1	DATE 2/14/2012	DR rc	DWG 34-PP1DB72A2	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PP1-DB7-2A2](#)