







PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040009	D16OAR11
2	1	F050407	50-004-07 INC 60VAC/DC
3	1	F050104	50-001-04 CONCAVE RED TRANSPARENT



PANEL MOUNTING



CONTACT CONFIGURATION



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲4. MECHANICAL LIFE: 2,000,000 OPERATIONS
5. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
6. OPERATING TEMP.: -25°C to 55°C
7. LAMP TYPE: 60V AC/DC INCANDESCENT
8. ▲ DENOTES CRITICAL PARAMETER.
9. PACKAGE: BOX/20 PER
10. 2002/95/EC (ROHS) COMPLIANT



A	17187	RELEASED FOR PRODUCTION	4/16/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16OAR11ERED				
SCALE 2:1	DATE 4/16/2007	DR TN	DWG XF0715P	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR11ERED](#)