





PARAMETERS	SYMBOL	MAX.	UNITS
LAMP VOLTAGE (AC)	V	125	V
STARTUP VOLTAGE	V _s	85	V
CURRENT	I	0.8	mA
SERIES RESISTANCE	R	120	ΩHMS



CIRCUIT: DPST

PANEL CUTOOUT
NOT TO SCALE

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.

X.XX=±0.25

3. RATING:

6A @250VAC;9A @125VAC {UL, CSA, VDE}

4(1)A @250VAC

4. LAMP VOLTAGE: 125V (NEON BULB)

5. MATERIAL:

CONTACT SURFACE: Coin Silver, Silver Plate

TERMINAL: Copper Alloy W/ Silver Plate.

6. CONTACT RESISTANCE: 20MILLIOHMS TYP. INITIAL


7. INSULATION RESISTANCE: 1000MegaOHMS

8. DIELECTRICAL STRENGTHS >1500V RMS min. @SEA LEVEL

>3000V RMS @SEA LEVEL

9. MECHANICAL LIFE: 50,000 CYCLES.

10. ELECTRICAL LIFE: 10,000 CYCLES.



E-SWITCH®				
TITLE				
R1973B BLK RED FF1				
SCALE	DATE	DR	DWG	REV
1.5:1	10/01/01	CJB	M400046	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1973BBLKREDFF1](#)