



SWITCH FUNCTION ▲

POS. 1	POS. 2	POS. 3
		
OFF	N/A	ON
OPEN	N/A	2-1, 5-4






RECOMMENDED PANEL MOUNTING

PANEL THICKNESS	X
1.2-1.8	29.9/30.0
1.8-2.4	30.3/30.4
2.4-3.0	30.7/30.8

CIRCUIT: DPST
FUNCTIONS

NOTES:

- ALL DIMENSIONS IN mm [INCH]
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERM. NOS. FOR REF. ONLY
- MECHANICAL LIFE: 50,000 CYCLES
- CONTACT RESISTANCE: <30 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: 1000V AC 1MIN
- ▲ DENOTES CRITICAL PARAMETER.
- INSULATION RESISTANCE: 500M OHMS AT 500VDC
- OPERATING TEMP: -20°C to 85°C
- ▲ 10. LAMP: 12VDC Incandescent
- RATING: IP66
- 2002/95/EC (ROHS) COMPLIANT

▲ BLUE FULL
ILLUMINATED
ROCKER▲ RUBBER GASKET
(Y000100)▲ BLACK
HOUSING▲ RUBBER PLUG
BOTH SIDES

B	20640	REMOVED RATING & RESISTOR	06/07/12	drg
A	20537	New Release	3/19/2012	MM
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE RBW2ABLKBILEF3

SCALE NONE

DATE 3/19/2012

DR mm

DWG Y100014

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RBW2ABLKBILEF3](#)