









PANEL MOUNTING



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. MECHANICAL LIFE: 2,000,000 OPERATIONS
5. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
- ▲ 6. OPERATING TEMP.: -25°C to 55°C
7. STORAGE TEMP: -40°C to 85°C
9. LAMP VOLTAGE: 6V DC GREEN LED
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT

PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040027	D16OAR12
2	1	F050416	50-004-16 6VDC GREEN LED
3	1	F051201	50-012-01 (MUSHROOM HEAD) GREEN



TITLE D16OAR2HGRNGRN

A	17792	RELEASED FOR PRODUCTION	10/22/07	BF
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1

DATE 10/22/2007

DR
BFDWG
XF0739PREV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR2HGRNGRN](#)