




CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	NONE	DN	
2-3,5-6	OPEN	2-1,5-4	

NOTES:

- 1. ALL DIMENSIONS IN MM
- 2. TERM. NOS. FOR REF ONLY
- 3. RATING: 0.4 (VA) Max. @20V Max. (AC or DC)

3. RATING: 0.4 (VA) Max. @20V Max. (AC or DC)			
A	RELEASED FOR PRODUCTION		
REV.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TOLERANCES			
0.0	±0.4		
0.00	±0.25		
TITLE			
300 DP-1 J6 (BLK.) V52 R E			
E-SWITCH®			
SCALE	DATE	DR	DWG
2:1	8/20/98	MM	T321042
			REV
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300DP1J6BLKVS2RE](#)