





RECOMMEND PANEL MOUNTING







CONTACT CONFIGURATION


NOTES:

- ALL DIMENSIONS IN MM [INCH].
- GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25

- TERM. NOS. FOR REF. ONLY.
- RATING: 5A @250VAC
8A @125VAC
.2A @250VDC
6A @24VDC
- ELECTRIC LIFE: 50,000 MAKE-OR-BREAK CYCLES AT FULL LOAD.
- INSULATION: 1,000 MΩ MIN.
- DIELECTRIC STRENGTH: 1,500V FOR 1 MIN
- OPERATING TEMP: -25°C TO 55°C
- LENS COLOR: BLUE
- LAMP VOLTAGE: 14V AC or DC (80 mA, INCANDESCENT)
- PANEL THICKNESS: 0.5 - 4 mm
- DEGREE OF PROTECTION: IP65
- 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



Parts List

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F060621	LAKOAV11
2	1	F051601	P16 PLASTIC TERM. PROTECTOR
3	1	F050404	14V AC/DC INCANDESCENT
4	1	F051702	25MM RING
5	1	F061257	25MM BLU LENS



TITLE LAKOAV11BBLU

SCALE 1:1

DATE 10/20/2006

DR BLR

DWG XF0757P

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	18139	RELEASED FOR PRODUCTION	6/20/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LAKOAV11BBLU](#)