


RECOMMENDED P.C.B. LAYOUT (SCALE 5:1)



CIRCUIT: SP2T

CONTACT CONFIGURATION

- | | |
|---|-----------------------------------|
| 1. ALL DIMENSIONS IN MM | 8. OPERATING TEMP, -20°C to +70°C |
| 2. TERM. NOS. FOR REF ONLY | 9. LIFE: 10,000 Cycles min. |
| 3. RATING: DC 4V, 0.3A | |
| 4. OPERATING FORCE: 150±70gf | |
| 5. CONTACT RESISTANCE: 70m Ohms Max. | |
| 6. INSULATION RESISTANCE: DC 100V-100M Ohms Min | |
| 7. WITHSTAND VOLTAGE: AC 100V-1MINUTE | |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				TITLE		EG 1257	
F	21709	ADDED TO DRAWING	10/29/14.	AS			
E	12175	ADD NOTE 8 & 9	5/22/02	CJB			
REV.	ECN No.	DESCRIPTION	DATE	CHKD			
					SCALE	DATE	DR
					10:1	8/27/97	MM
							DWG
							P112221
							REV
							F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[EG1257](#)