


RECOMMENDED P.C.B. LAYOUT






CIRCUIT: 2PDT

| SWITCH FUNCTION | | |
|-----------------|--------|---------|
| PDS. 1 | PDS. 2 | PDS. 3 |
| | | |
| DN | NONE | DN |
| 2-3,5-6 | DPEN | 2-1,5-4 |

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 3A@ 120VAC. OR 28VDC:
1A@ 250VAC.
5. FIXED TERMINAL & MOVING CONTACT:
COPPER ALLOY w/ Silver plate
6. ELECTRIC LIFE: 30,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to +85°C
10. 2002/95/EC (ROHS) COMPLIANT



| | | | | |
|------|---------|-----------------------------|--------|------|
| C | 17449 | REMOVED MARKING DN ACTUATOR | 7/9/07 | TN |
| B | 12341 | REVISED AND REDRAWN | 8/2/02 | CJB |
| REV. | ECN No. | DESCRIPTION | DATE | CHKD |

| | | | | |
|-------|--------|------------------|---------|-----|
| TITLE | | 400MDP1R1BLKM6QE | | |
| SCALE | DATE | DR | DWG | REV |
| 2:1 | 7/9/07 | TN | T421003 | C |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[400MDP1R1BLKM6QE](#)