






RECOMMEND PANEL MOUNTING



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY.
4. RATING: 5A @250VAC  
8A @125VAC  
.2A @250VDC  
6A @24VDC
5. INSULATION: 1,000 MΩ MIN.
6. DIELECTRIC STRENGTH: 2000V FOR 1 MIN.
7. SEALED TO IP65.
8. TRAVEL: 3.0MM FULL TRAVEL, 2.0MM LATCH
9. ELECTRICAL LIFE: >50,000 CYCLES
10. OPERATING TEMP: -25C TO +70C
11. PANEL THICKNESS: 0.5MM TO 3.0MM
12. LAMP VOLTAGE: NONE
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2002/95/EC (ROHS) COMPLIANT



▲ SPDT  
CONTACT CONFIGURATION

| ▲ Parts List |     |             |                           |
|--------------|-----|-------------|---------------------------|
| ITEM         | QTY | PART NUMBER | DESCRIPTION               |
| 1            | 1   | F060610     | LASOAU11 BODY             |
| 2            | 1   | F051706     | 35MM FLUSH MOUNT BEZEL    |
| 3            | 1   | F051707     | 35MM FLUSH MOUNT RETAINER |
| 4            | 1   | F060214     | 29MM RED LENS             |



|     |        |                          |          |    |
|-----|--------|--------------------------|----------|----|
| C   | 21842  | change 40.5 dim. callout | 5/5/2015 | MW |
| B   | 17530  | REVISED AND REDRAWN      | 8/3/07   | BF |
| REV | PCR NO | DESCRIPTION              | DATE     | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LASOAU310RED

SCALE 1:1

DATE 8/3/2007

DR BF

DWG XF0731P

REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[LASOAU310RED](#)