


▲ ACCESSORY (ACC-F03-1)
PVC CAP - CLEAR
with BLACK FRAME




▲ LENS COLOR: GREEN
FULL ILLUMINATION



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	1-3, 2



CIRCUIT: SPST



▲ BODY
COLOR: BLACK



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = 0.4
X.XX = 0.25
- TERMINAL NUMBERS FOR REFERENCE ONLY.
- CONTACT RATINGS:
 - 16A 125VAC [UL, cUL]
 - 3/4HP 250VAC [UL, cUL]
 - 16(6)A 250V~ 1E4 T125 [VDE]
 - 10(4)A 250V~ 5E4 T125 [VDE]
- CONTACT RESISTANCE: 35mΩ MAX. INITIAL @ 50VAC
- INSULATION RESISTANCE: 100MΩ @ 500VDC
- DIELECTRIC STRENGTH: 1500VAC FOR 1 MINUTE
- ELERTICAL LIFE: 6,000 CYCLES [UR,cUR]
10,000 CYCLES [VDE]
50,000 CYCLES [VDE]
- ▲ DENOTE CRITICAL PARAMETER
- 2011/65/EU (ROHS) COMPLIANT
- ILLUMINATION VOLTAGE: 125V
- LENS COLOR: GREEN



A	23233	Release	2/28/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PR141C1000-136-ACC-F03-1

SCALE
1:1

DATE
2/28/2018

DR
MW

DWG
38-PR1S00267

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PR141C1000-136-ACC-F03-1](#)