





NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 20A @125VAC;
16A @250VAC.
5. ELECTRICAL LIFE: 10,000 CYCLES MIN.
6. CONTACT RESISTANCE: 20 Milli-OHMS MAX.
7. OPERATING TEMP: -20°C TO 85°C
8. DIELECTRIC STRENGTH: >1,000V AC 1MIN
9. LAMP VOLTAGE: NONE
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT.

OBSELETE
January 2018
PCR 23169



TITLE RSCF141D1100

A	20715	New Release	8/23/12	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5 : 1	DATE 8/23/2012	DR RC	DWG 38-RSCF141D1100	REV A
------------------	-------------------	----------	------------------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[RSCF141D1100](#)