





RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-1	OPEN	2-3

NOTES:

1. ALL DIMENSIONS IN MM
2. TERM. NOS. FOR REF. ONLY
3. RATING: 0.4VA MAX. @20VAC OR DC MAX.
4. CRIMP METAL RETAINING BRACKET

TOLERANCES	±0.4	±0.25
0.0	0.00	0.00

E-SWITCH®

TITLE

500A SSP-1 M2 R E

SCALE

2:1

DATE

9/3/97

DR

MM

DWG

T511000

REV

C

C	DIM FROM 8.79 TO 9.20	10/30/18	MJR
B	CREATED NOTES	7/5/05	JB
REV.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[500ASSP1M2RE](#)