









PANEL MOUNTING



CONTACT CONFIGURATION



PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040020	D16EES12
2	1	F050419	50-004-19 12VDC GREEN LED
3	1	F050302	50-003-02 TRANSPARENT GREEN SQUARE (CONCAVE) LENS

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: 5A@ 250VAC
8A@ 125VAC
6A@ 24VDC
5. ELECTRICAL LIFE: 50,000 OPERATIONS
6. OPERATING TEMP.: -25°C to 55°C
- ▲ 7. LAMP VOLTAGE: 12VDC GREEN LED
8. ▲ DENOTES CRITICAL PARAMETER.
9. DEGREE OF PROTECTION: IP 40
10. PANEL THICKNESS: 0.5 - 5.0mm
11. TRAVEL: 3.0mm FULL TRAVEL
12. PACKAGE: BOX/20 PCS

B	23625	correct Lamp color in notes	10/9/18	MW
A	18816	Release For Production	3/17/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE D16EES12JGRNGRN

SCALE 3:2

DATE 3/17/2010

DR BLR

DWG XF0816P

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16EES12JGRNGRN](#)