





RECOMMENDED P.C.B. LAYOUT






CIRCUIT: 2PDT

| SWITCH FUNCTION |         |
|-----------------|---------|
| PDS 1           | PDS 2   |
|                 |         |
| ON              | (ON)    |
| 2-1,5-4         | 2-3,5-6 |

( ) = Momentary

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.1A @30V DC
5. TRAVEL: TRAVEL=2.50±0.38  
LOCK=1.34±0.38
6. OPERATING FORCE: 180±50gf
7. CONTACT RESISTANCE: 50mILLI-Ohms MAX. Initially
8. ELECTRICAL LIFE (at Full Load):  
10,000 Cycles Make & Break
- ▲ 9. DESIGNATE MAJOR FEATURE:



E-SWITCH®

TITLE

TL2201DAZB1RBLK (Momentary)

SCALE

2:1

DATE

6/5/19

DR

CB

DWG

XP0172P

REV

A

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2201OAZB1RBLK](#)