





CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: SILVER PLATED COPPER ALLOY
5. CONTACT RATING: 0.3A @ 125V AC
6. CONTACT RESISTANCE: < 50m OHMS
7. OPERATING FORCE: 0.8 ± 0.3 Kg-cm
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT 4P: 4 POLE: 3 POSITIONS, 30° INDEX
10. DIELECTRIC STRENGTH: AC500V - 1 MIN.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING
12. ▲ DENOTES CRITICAL PARAMETER.



B	20435	CORRECT FLAT POSITION ON ACTUATOR	2/1/12	BGL
A	20073	RELEASED FOR PRODUCTION	7/29/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC43A13.001NLS

SCALE 1.5:1

DATE 7/29/2011

DR BGL

DWG G510282

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC43A13.001NLS](#)