





CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: GOLD FLASH OVER SILVER PLATE
5. CONTACT RATING: 0.3A @ 125V AC
6. CONTACT RESISTANCE: < 50m OHMS
7. OPERATING FORCE: 0.8 ± 0.3 Kg-cm
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT 4P: 4 POLE: 3 POSITIONS, 30° INDEX
10. DIELECTRIC STRENGTH: AC500V - 1 MIN.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT
12. ▲ DENOTES CRITICAL PARAMETER.



TITLE KC43A30.001NLF

A	20428	RELEASED FOR PRODUCTION	1/26/12	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
1.5:1	1/26/2012	BGL	G510283	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC43A30.001NLF](#)