





SHEET 1 OF 1

SCHEMATIC



SPECIFICATIONS

FUNCTION:
2P1T OFF-ON
Auto OFF Below Calibration Voltage

RATINGS:
ANSI/UL 508 and CAN/CSA C22.2 No.14 (E195908):
16A 120VAC [cURus]
12A 120VAC [cURus]
1/2HP 120VAC (9.8A FLA, 56.6A LRA) [cURus]

CALIBRATION VOLTAGE:
Use: 120V 60Hz
Release: 55-75V

ELECTRICAL LIFE:
6,000 Cycles [cURus]

INGRESS PROTECTION:
IP55

APPROVALS:
 

COLORS AND MARKINGS

BEZEL:
Black

ACTUATOR:
ON: Green
OFF: Red

MARKING:
I/O Vertical (1)

MARKING COLOR:
White

MATERIALS

UPPER BODY:
Polyamide 6/6 (PA66)

LOWER BODY:
Polyamide 6/6 (PA66+G10)

BEZEL:
Polyamide 6/6 (PA66+G10)

ACTUATORS:
Polyamide 6/6 (PA66)

MOUNTING EARS:
Polyamide 6/6 (PA66)


COVER:
Polyvinyl Chloride (PVC)

CONTACTS:
Silver Alloy Clad Copper (AgSnO/Cu)

TERMINALS:
Brass

GASKET:
Rubber

SUGGESTED PANEL CUTOUT




BODY	A	09/08/07	CAB
COLORS	A	09/08/07	CAB
MATERIALS	A	09/08/07	CAB
SPECIFICATIONS	A	09/08/07	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	INITIAL RELEASE	PCRD0051	09/08/10	CAB
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.020 [±0.5] / ±1°
SCALE	DRAWING NOT TO SCALE
PROJECTION	

	
KJD17-21213-112	
DRAWING NUMBER	34-KJD1721213112
DATE	AUGUST 10, 2009
REVISION	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KJD17-21213-112](#)