


SHEET 1 OF 1

SCHEMATIC



SPECIFICATIONS


FUNCTION:
2P1T OFF-ON
Auto OFF Below Calibration Voltage

RATINGS:
ANSI/UL 508 and CAN/CSA C22.2 No.14 (E195908):
16A 220-240VAC [cURus]
2HP 220-240VAC (12A FLA, 72A LRA) [cURus]

CALIBRATION VOLTAGE:
Use: 230V 50Hz
Release: 120-160V

ELECTRICAL LIFE:
6,000 Cycles [cURus]

INGRESS PROTECTION:
IP55

APPROVALS:
 **RoHS**
COMPLIANT

COLORS AND MARKINGS

BEZEL:
Black

ACTUATOR:
ON: Green
OFF: Red

MARKING:
I/O Vertical (1)

MARKING COLOR:
White

MATERIALS

UPPER BODY:
Polyamide 6/6 (PA66)

LOWER BODY:
Polyamide 6/6 (PA66+G10)

BEZEL:
Polyamide 6/6 (PA66+G10)

ACTUATORS:
Polyamide 6/6 (PA66)

MOUNTING EARS:
Polyamide 6/6 (PA66)


COVER:
Polyvinyl Chloride (PVC)

CONTACTS:
Silver Alloy Clad Copper (AgSnO/Cu)

TERMINALS:
Brass

GASKET:
Rubber


SUGGESTED PANEL CUTOUT



BODY	A	09/08/07	CAB
COLORS	A	09/08/07	CAB
MATERIALS	A	09/08/07	CAB
SPECIFICATIONS	A	09/08/07	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	INITIAL RELEASE	19420	10/11/09	CAB
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.020 [±0.5] / ±1°
SCALE	DRAWING NOT TO SCALE
PROJECTION	

 E-SWITCH	
TITLE KJD17-21313-112	
ITEM NUMBER 34-KJD1721313112	DATE NOVEMBER 9, 2010
REVISION A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KJD17-21313-112](#)