







P.C.B. MOUNTING LAYOUT





CIRCUIT: SPST

NOTES:

1. GENERAL TOLERANCE: $x.x \pm 0.4$
 $x.xx \pm 0.25$
2. RATING: 50mA@12VDC
3. TRAVEL: 0.35 ± 0.2 mm
4. CONTACT RESISTANCE: 100m OHMS
5. LIFE CYCLES: 500,000 CYCLES
- ▲ 6. OPERATING FORCE: 160 ± 50 gf
7. ▲ DENOTES CRITICAL PARAMETER
8. PACKAGE: TAPE AND REEL, 1900 PIECES PER REEL
9. 2002/95/EC (ROHS) COMPLIANT
- ▲ 10. CONTACT MATERIAL: SILVER



ISOMETRIC



				
TITLE TL6700NF160QJ				
SCALE	5:1	DATE	11/14/2006	DR TN
DWG	P010464	REV	B	

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL6700NF160QJ](#)