







RECOMMENDED P.C.B. LAND



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
~UNLESS OTHERWISE SPECIFIED
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NOS FOR REF. ONLY
4. TRAVEL: 0.25 ± .1mm
5. ▲ RATING: 50mA, 12VDC (GOLD CONTACTS)
6. OPERATING FORCE: 160±50gf
7. CONTACT RESISTANCE: 100M OHM MAX.
8. ▲ PACKAGED: TAPE & REEL, 1500
9. ▲ DESIGNATE MAJOR DIMENSIONS
10. 2002/95/EC (ROHS) COMPLIANT



10. 2002/95/EC (ROHS) COMPLIANT				
C	16646	UPDATED NOTES	11/13/06	TN
B	11904	REVISED AND REDRAWN	7/9/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

				
TITLE		TLE3303F160QG		
SCALE	DATE	DR	DWG	REV
4:1	11/13/2006	TN	P010525	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TLE3303F160QG](#)