








RECOMMEND P.C.B. LAYOUT



Coplanar w/in 0.10 (.004") Total.
5 Terminals



CIRCUIT, SPST

CONTACT CONFIGURATION

NOTES

- 1. ALL DIMENSIONS IN MM
- 2. TERM. NOS. FOR REF ONLY
- 3. RATING: DC 12V, 50mA
- 4. TRAVEL: 0.25 +0.2/-0.1mm
- 5. CONTACT RESISTANCE: 100m Ohms Typical.

TOLERANCES			
		±0.4	
		±0.25	
TITLE			
TLE 3303 F100 Q G			
E-SWITCH®			
REVISED & REDRAWN			
C	9/17/98		
DESCRIPTION			
REV.	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMITTED			
SCALE			
4:1	DATE	DR	DWG
	5/29/97	MM	P010528
REV			
C			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TLE3303F100QG](#)