









P.C.B MOUNTING



CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERMINAL NUMBERS FOR REF ONLY.
4. TRAVEL: 0.25mm +0.2/-0.1
5. RATING: 50mA, 12VDC
6. OPERATING FORCE: 160± 50gf
7. CONTACT RESISTANCE: 100Milli-OHM MAX.
8. INSULATION RESISTANCE: 100 Mega-OHMS MIN.
9. DIELECTRIC STRENGTH: 250 VAC MIN.
10. LIFE EXPECTANCY: 100,000 TYPICAL
- ▲ 11. ACTUATOR COLOR: BLACK
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. PACKAGING: TAPE AND REEL 1,200 PCS PER
14. 2002/95/EC (ROHS) COMPLIANT



A	20458	Release For Production	02/09/11	BMA
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

 E-SWITCH®				
TITLE TLE3303AF160QG				
SCALE 4:1	DATE 2/9/2012	DR BMA	DWG P010662	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TLE3303AF160QG](#)