







RECOMMENDED P.C.B. LAYOUT



NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERM. NOS. FOR REFERENCE ONLY.
- CONTACT RATING: 50mA @12VDC
- TRAVEL: $0.25 \pm 0.2/-0.1$ mm
- CONTACT RESISTANCE: 100mILLI-OHMS Max.
- OPERATING FORCE: 100 ± 50 gf 
- CONTACT MATERIAL: SILVER
- ▲ DENOTES CRITICAL PARAMETER.
- ACTUATOR: 3.15 mm
- PACKAGE: TRAY/ 200 PIECES PER
- 2002/95/EC (ROHS) COMPLIANT



E-SWITCH™

TITLE TL53F100Q

B	19692	CORRECTED OPERATING FORCE	2/18/11	BGL
A	19630	RELEASED FOR PRODUCTION	1/31/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	2:1	DATE	1/31/2011	DR	BGL	DWG	P010693	REV	B
-------	-----	------	-----------	----	-----	-----	---------	-----	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL53F100Q](#)