


P.C. MOUNTING

▲	O.P. (MM)	P.T. (MM)
C	9.5 ± 0.8	1.8 MAX.



O.P. = OPERATING POINT
P.T. = PRE-TRAVEL




CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- RATING: 0.1A @ 5VDC
- OPERATING FORCE: 50± 12 GRAMS
- OPERATING TEMP: -25°C TO 85°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 300,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS
- DIELECTRIC STRENGTH: 1000VAC-MIN.
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT
- CONTACT MATERIAL: SILVER



ISOMETRIC



C	20204	UPDATE DRAWING	10/11/11	BMA
B	17479	REVISED AND REDRAWN	7/17/07	BF
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE DM085Q102F050P1A

SCALE 4:1

DATE 7/17/2007

DR BF

DWG P030019

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[DM085Q102F050P1A](#)