


P.C. MOUNTING



▲	O.P. (MM)	P.T. (MM)
▲	6.8 ± 0.1	1.8 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL




NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- RATING: 0.1A @5V DC
- OPERATING FORCE: 30gf
- OPERATING TEMP: -25°C TO 85°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- MECHANICAL LIFE: 300,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS
- DIELECTRIC STRENGTH: 1000V RMS AT SEA LEVEL
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT
- CONTACT MATERIAL: SILVER



ISOMETRIC



TITLE DM085Q101F030P1A

SCALE 4:1

DATE 7/31/2007

DR BF

DWG P030020

REV D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

D	20203	UPDATE DRAWING	10/11/11	BMA
C	17520	REVISED AND REDRAWN	7/31/07	BF
REV	PCR NO	DESCRIPTION	DATE	BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[DM085Q101F030P1A](#)