







SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
2-1, 5-4	2-3, 5-6



HOLE USED TO
IDENTIFY TERMINALS



NOTE:

1. ALL DIMENSIONS IN mm [INCH]
2. GENERAL TOLERANCE: $x.x = \pm 0.4$
 $x.xx = \pm 0.25$
3. TERMINAL NUMBERS FOR REF. ONLY
- ▲ 4. CONTACT RATING: 0.1A @ 30 VDC
5. TRAVEL: FULL= 1.8mm; LOCKING= 1.2mm
- ▲ 6. OPERATING FORCE: 200±80gf
7. ELECTRICAL LIFE: 10,000 CYCLES
8. CONTACT RESISTANCE: 30mΩ MAX.
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. 2002/95/EC (RoHS) COMPLIANT



TITLE JN2UEENAGX

SCALE 3:1

DATE 5/16/2013

DR rc

DWG P200001

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	21131	Re-Release Part Number	5/16/13	rc
REV	PCR NO	DESCRIPTION	DATE	BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

JN2UEENAGX