




CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲5. OPERATING FORCE: 160 ± 50 gms
- ▲6. TRAVEL: 0.25mm +0.1/-0.1
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 200,000 CYCLES MIN.
9. PACKAGE: TAPE AND REEL - 3300 PIECES PER REEL
10. ▲DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT.



|                                                                                                              |        |             |         |    |                     |                   |          |                |          |
|--------------------------------------------------------------------------------------------------------------|--------|-------------|---------|----|---------------------|-------------------|----------|----------------|----------|
| A                                                                                                            | 20976  | New Release | 1/18/13 | rc | TITLE TL1014AF160QG |                   |          |                |          |
| REV                                                                                                          | PCR NO | DESCRIPTION | DATE    | BY |                     |                   |          |                |          |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |        |             |         |    | SCALE               | DATE<br>1/18/2013 | DR<br>rc | DWG<br>P410000 | REV<br>A |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL1014AF160QG](#)