


## SCHEMATIC



## SPECIFICATIONS

FUNCTION:  
1P2T ON[1]-ON[2]-(ON[1])

RATING:  
ANSI/UL 1054 and CAN/CSA C22.2 No.55 (E194579):  
16A 125VAC [cURus]  
12A 250VAC [cURus]  
1HP 125/250VAC [cURus]

CONTACT RESISTANCE:  
Initial: 10mΩ Max.

TEMPERATURE:  
Operating: 0°C to 85°C [cURus]

ELECTRICAL LIFE:  
6,000 Cycles [cURus]

APPROVALS:



## COLORS

BODY:  
White

ACTUATOR:  
White

## MATERIALS

BODY:  
Polyamide 6/6 (PA66)

ACTUATOR:  
Polyamide 6/6 (PA66)

SPRING:  
Steel (65Mn)

HOOK SPRING:  
Stainless Steel (1Cr13)


ACTUATION LEVER:  
Brass (H62)

MOBILE CONTACT BAR:  
Silver Plated Copper


MOBILE CONTACT:  
Silver/Nickel (AgNi(10))

STATIONARY CONTACT:  
Silver/Nickel Clad Copper (AgNi(10)/Cu)

TERMINALS:  
Silver Plated Brass (H62)



## SUGGESTED PANEL CUTOUT



ACTUATOR	B	10/03/16	CAB
BODY	B	10/03/24	CAB
COLORS	A	08/10/23	CAB
MATERIALS	B	10/04/07	CAB
SPECIFICATIONS	-	-	-
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	INITIAL RELEASE	22582	11/9/16	MW
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

## DIMENSIONS

INCHES [MILLIMETERS]

GENERAL TOLERANCES

±0.008 [±0.2] / ±1"

SCALE

DRAWING NOT TO SCALE

PROJECTION

ITEM NUMBER


34-PP1FT72B2

DATE

11/9/16

REVISION

A



PP1-FT7-2B2

DATE

11/9/16

REVISION

A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PP1-FT7-2B2](#)