




▲

SWITCH FUNCTION	
POS. 1	POS. 2
1-2 ON	1-2 OFF
3-4 OFF	3-4 ON




3 ○ ○ 4
 GREEN (FORWARD)
 (+) ○ (-)
 GREEN (REVERSE)


▲ DPDT ON-ON
 CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NOS. FOR REF. ONLY
- ▲ 4. FUNCTION: DPDT
- ▲ 5. RATING: 2A @ 48VDC
6. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
7. INSULATION RESISTANCE: 1,000M Ω @ 500VDC
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. ELECTRICAL LIFE: 50,000 CYCLES
10. OPERATING TEMPERATURE: -20°C TO 55°C
11. INGRESS PROTECTION: IP65
12. SUPPLIED HARDWARE: O-RING AND HEXNUT
13. ▲ DENOTES CRITICAL PARAMETER
- ▲ 14. ILLUMINATION VOLTAGE: 2.8V (FORWARD), 2.8V (REVERSE)



DOT DENOTES
 LED COLOR



B	24607	HOUSING UPDATE	11/23/20	JM
A	23525	NEW RELEASE	8/13/18	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
 TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV10F2U0SS-331

SCALE 2:3	DATE 8/13/2018	DR MJR	DWG 52-PV10F2U0SS331	REV B
--------------	-------------------	-----------	-------------------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV10F2U0SS-331](#)