



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. CONTACT RESISTANCE: 1 OHM MAX.
4. RATING: 1A @ 5-24VDC
5. ELECTRIC LIFE: 50,000,000 CYCLES
6. OPERATING TEMP.: -20°C to 65°C
7. ▲ DENOTES CRITICAL PARAMETER.
8. HARDWARE SUPPLIED: O-RING and HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101926	UPDATE NOTES	05/19/23	JS	TITLE PZ7M2CNNW150				100117260
					SCALE	DATE	DR	DWG	REV
					1:1	6/11/2021	MW	T070103	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PZ7M2CNNW150](#)