











SWITCH FUNCTION	
POS. 1	POS. 3
OFF	ON
OPEN	1a - 1



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 15A @125VAC; 8A @250VAC cURus
6A 250V VDE
- ▲ 5. LAMP COLOR: RED LED
6. MATERIAL: CONTACT: COIN SILVER, SILVER PLATED
TERMINAL: COPPER ALLOY W/SILVER PLATE
7. ELECTRICAL LIFE: 10,000 CYCLES
8. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
9. DIELECTRIC STRENGTH: >1,500V AC 1 MIN
10. OPERATING TEMP.: -30°C to 80°C
11. ▲ DENOTES CRITICAL PARAMETER.



▲ LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	2.0
LUMINOUS INTENSITY	mcd	20 typ.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-101554	PRINT UPDATE	01/11/23	JS	TITLE R1966ABLKBLKEPRED				000016560
					SCALE 2:1	DATE 7/6/2000	DR GLG	DWG M300101	REV C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1966ABLKBLKEPRED](#)