






## RECOMMENDED PANEL MOUNTING

| PANEL THICKNESS | X± 0.05     |
|-----------------|-------------|
| 0.75-1.25       | 29.6-29.7   |
| 1.25-2.00       | 30.1-30.2   |
| 2.00-3.00       | 30.45-30.55 |

| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| ON              | OFF    |
| 1-1a            | OPEN   |



## NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE:  $X.X \pm 0.4$   
 $X.XX \pm 0.25$
- TERM. NOS. FOR REF. ONLY
- RATING: 20A 125VAC, 16A 250VAC UL APPROVED
- ELECTRICAL LIFE: OVER 10,000 CYCLES
- MECHANICAL LIFE: OVER 30,000 CYCLES
- CONTACT RESISTANCE:  $< 20 \text{ m}\Omega$  (INITIAL)
- DIELECTRIC STRENGTH:  $> 1500 \text{ V}$  1 min
- INSULATION RESISTANCE:  $> 1,000 \text{ m}\Omega$  @ 500V DC
- LAMP VOLTAGE: NEON-250VAC
- OPERATING TEMPERATURE: TERMINAL SIDE  $-20^\circ\text{C}$  to  $85^\circ\text{C}$   
ROCKER SIDE  $-20^\circ\text{C}$  to  $55^\circ\text{C}$
- ▲ DENOTES CRITICAL PARAMETER

| REV | ECO NO     | DESCRIPTION                     | DATE     | BY | E-SWITCH®          |                |       |             | OBJECT ID |
|-----|------------|---------------------------------|----------|----|--------------------|----------------|-------|-------------|-----------|
| D   | ECO-100524 | REMOVE VDE/ENEC RATING AND LOGO | 02/03/22 | JS | TITLE R4JBLKRILEF2 |                |       |             | 000016419 |
|     |            |                                 |          |    | SCALE 1:1          | DATE 2/20/2006 | DR PH | DWG M041001 | REV D     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R4JBLKRILEF2](#)