


R7 SERIES ROCKER SWITCH


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS



Marine



Construction Equipment



Agricultural Equipment



Recreational Vehicles



Landscaping Equipment



Industrial Equipment



RoHS

SPECIFICATIONS

Contact Rating: 20(8)A @ 125/250VAC, 50/60 Hz, μ T55;
16A @ 6-30VDC, 50/60 Hz, μ T55;
20(8)A @ 125/250VAC, 50/60 Hz, μ T85/T55;
16A @ 6-30VDC, 50/60 Hz, μ T85/T55
Electrical Life: 10,000 Cycles per UL61058
Contact Resistance: 20m Ω Max. initial
Insulation Resistance: 100 M Ω Min. @ 500VDC
Dielectric Strength: 1,500VAC for 1 minute
Operating Temperature: 0°C to 55°C
Storage Temperature: -20°C to 85°C
Agency Approvals: cURus
Contact Arrangement: SP or DP up to 3 positions
Moisture Protection: IP67 to front panel
Panel Thickness: 1.5 - 4.5mm

FEATURES & BENEFITS

- Rated to IP67
- UL Certified
- Ergonomic design
- Solder, faston or screw termination
- LED Illumination options
- Multiple functions
- Many actuator styles
- Custom actuator marking available

PART NUMBER CONFIGURATOR

Series	No. of Poles	Functions	Terminals	Actuator Style**	Marking**	Lamp Type	Actuator Color**	Ratings/Temp	LED 1 Color	LED 2 Color	Lens Color**
R7	1 - SP 2 - DP	1 - On-Off 2 - On-On 3 - On-Off-On* W - Screw 4 - (On)-Off 5 - (On)-On 6 - (On)-Off-(On) 7 - (On)-Off-On 8 - On-(Off)	F - Faston 1/4" S - Solder Lug W - Screw	XX - None A1 - Hard PC A2 - Hard PC A3 - Hard PC B1 - Soft TPR B2 - Soft TPR B3 - Soft TPR B4 - Soft TPR C1 - Hard PC C2 - Hard PC C3 - Hard PC D1 - Hard PC D2 - Hard PC D3 - Hard PC E1 - Soft TPR E2 - Soft TPR E3 - Soft TPR F1 - Soft TPR F2 - Soft TPR F3 - Soft TPR	SXXX	N - None 1 - 6VDC 2 - 12VDC 3 - 24VDC 4 - 125VAC 5 - 250VAC	X - None B - Black G - Gray	B - 20(8)A @ 125/250VAC, 50/60 Hz, μ T55 D - 16A @ 6-30VDC, 50/60 Hz, μ T55 2 - 20(8)A @ 125/250VAC, 50/60 Hz, μ T85/T55* 4 - 16A @ 6-30VDC, 50/60 Hz, μ T85/T55*	N - None R - Red A - Amber G - Green	N - None R - Red A - Amber G - Green	X - None W - White G - Green
() denotes momentary											
* Function 3 is used only with ratings options 2 and 4											
** When creating a part number for just the switch body, choose the "X" options for those marked in red. Use all options in the main part number configurator when ordering the switch body assembled with the actuator.											
EXAMPLE ORDERING CODES: Complete Switch: R712FB1-SXXXNBBNNX R711FB2-SXXX2BDANW Switch Body: R712FXX-SXXX2XGRX R711FXX-SXXXNXDNNX Switch Actuator: R7F3BLKW R7A1BLKX											

ACTUATOR CONFIGURATOR*

Series	Actuator Style	Actuator Color	Lens Color	Marking
R7	XX A1 A2 D1 A3 D2 B1 D3 B2 E1 B3 E2 B4 E3 C1 F1 C2 F2 C3 F3	BLK - Black GRY - Gray	X - None W - White G - Green	SXXX

*You can choose to order just the actuator as a separate part number

Specifications subject to change without notice






E-SWITCH®

www.e-switch.com




800.867.2717

2

BODY DIMENSIONS




**Double Pole
without actuator**



**Double Pole
with actuator**

(E3 actuator shown)



TERMINATION OPTIONS

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

**ROCKER
SWITCHES**

ROTARY
SWITCHES







SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES




TOGGLE
SWITCHES

CAP
OPTIONS



FASTON 1/4"

SCREW



SOLDER



E-SWITCH®

www.e-switch.com

800.867.2717

4

R7 SERIES ROCKER SWITCH

ACTUATOR OPTIONS

A Hard PC



A1



A2



A3

B Soft TPR



B1



B2



B3



B4

C Hard PC



C1



C2



C3

D Hard PC



D1



D2



D3

E Soft TPR



E1



E2



E3

F Soft TPR



F1



F2



F3

TPR = Thermal Plastic Rubber

PC = Polycarbonate

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS



E-SWITCH®

www.e-switch.com

800.867.2717

5


R7 SERIES ROCKER SWITCH

SCHEMATICS




SPST
Non Illuminated

For R711, R714, R718




SPDT
Non Illuminated

For R712, R713, R715,
R716, R717




SPST
with LED #1

For R711, R714, R718




SPDT
with 2 LEDs

For R712, R713, R715,
R716, R717




SPDT
with LED #1

For R712, R713, R715,
R716, R717




SPDT
with LED #2

For R712, R713, R715,
R716, R717




DPST
Non Illuminated

For R721, R724, R728




DPDT
Non Illuminated

For R722, R723, R725,
R726, R727




DPST
with LED #1

For R721, R724, R728




DPDT
with 2 LEDs

For R722, R723, R725,
R726, R727



DPDT
with LED #1

For R722, R723, R725,
R726, R727



DPDT
with LED #2

For R722, R723, R725,
R726, R727



E-SWITCH®

www.e-switch.com

800.867.2717

6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[R723FF3-SXXX4B2RRW](#) [R711FB2-SXXX3BDGNW](#) [R711FXX-SXXXNXBNNX](#) [R713FE3-SXXX1B4RAW](#) [R713FE3-SXXX4B2RGW](#) [R713SB4-SXXX2B4GRW](#) [R713WE3-SXXX4B2RRW](#) [R713WE3-SXXX4G2GGW](#) [R723SF3-SXXX4B2GRW](#) [R713FA3-SXXX1B4RAW](#) [R723FB4-SXXX2B4AAW](#) [R727FC1-SXXXNBBNNX](#) [R711FB2-SXXX4BBGNW](#) [R716FB4-SXXX2BDRAW](#) [R711FE1-SXXX1BDGNW](#) [R713FF3-SXXX1B4RAW](#) [R713WE3-SXXX4B2GGW](#) [R713WE3-SXXX4G2RRW](#) [R714FE1-SXXX3BDANX](#) [R722SF3-SXXX4BBGRW](#) [R721FXX-SXXXNXBNNX](#) [R723FA1-SXXXNB4NNX](#) [R723FE1-SXXX2B4GNW](#) [R723FF3-SXXX2B4RRW](#) [R726FA3-SXXX3BDGRW](#)