


| ▲ SWITCH FUNCTION |        |          |
|-------------------|--------|----------|
| POS. 1            | POS. 2 | POS. 3   |
|                   |        |          |
| (ON)              | OFF    | ON       |
| 1-2; 4-5          | OFF    | 2-3; 5-6 |




CIRCUIT: DPDT  
(ON) - OFF - ON





( ) = MOMENTARY FUNCTION

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 20(8)A @125/250VAC 50/60 Hz,  $\mu$ T55  
UL LISTED
5. ELECTRICAL LIFE: 10,000 CYCLES
6. MECHANICAL LIFE: 30,000 CYCLES
7. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
8. DIELECTRIC STRENGTH: >1,500V AC 1MIN
9. INSULATION RESISTANCE: >100 MOHMS @ 500VDC
10. OPERATING TEMP: 0°C to 55°C
11. LED VOLTAGE: NONE
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



RECOMMENDED  
PANEL CUT-OUT



TITLE R727FC1-SXXXNBBNNX

|     |        |                 |         |     |
|-----|--------|-----------------|---------|-----|
| A   | 21398  | INITIAL RELEASE | 3/10/14 | EBP |
| REV | PCR NO | DESCRIPTION     | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |                   |           |                |          |
|-------|-------------------|-----------|----------------|----------|
| SCALE | DATE<br>3/10/2014 | DR<br>EBP | DWG<br>C700022 | REV<br>A |
|-------|-------------------|-----------|----------------|----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R727FC1-SXXXNBBNNX](#)