






RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS 1-6mm



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 36 VDC
6. ELECTRIC LIFE: 200,000 CYCLES
7. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
8. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
9. OPERATING TEMP.: -20°C to 70°C
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LAMP VOLTAGE: RED 20mA 2.0V TYP., GREEN 20mA 3.1V TYP.
13. TRAVEL: 1.80mm
14. ACTUATION FORCE:  $4.5 \pm 1.5$  N
15. MOUNTING NUT TORQUE: 1-3 Nm
16. INGRESS PROTECTION: IP67, IK10
17. HARDWARE SUPPLIED: O-RING AND HEXNUT



| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®          |           |     |         | OBJECT ID |
|-----|------------|--------------|----------|----|--------------------|-----------|-----|---------|-----------|
| D   | ECO-101750 | print update | 03/20/23 | MW | TITLE SV4F23SS-6G1 |           |     |         | 000025964 |
|     |            |              |          |    | SCALE              | DATE      | DR  | DWG     | REV       |
|     |            |              |          |    | 1:1                | 11/5/2019 | MJR | T840001 | D         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[SV4F23SS-6G1](#)