





NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. TERMINAL NUMBERS FOR REF. ONLY
3. TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
4. RATING: 12VDC @ 50mA
5. TRAVEL: 0.25 +0.2/-0.1
- ▲ 6. OPERATING FORCE: 100 $\pm$ 50gf
7. ELECTRICAL LIFE: 100,000 LIFE CYCLES
8. CONTACT RESISTANCE: 100m Ω MAX.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100047	XP0214A TITLE TO XP0214P	04/16/21	MR	TITLE TL1105SPF100Q1RBLK				100112159
					SCALE	DATE	DR	DWG	REV
					4:1	4/13/2021	JM	XP0214P	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL1105SPF100Q1RBLK](#)