





CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 160 ± 50 gms
6. TRAVEL: 0.25mm +0.2/-0.1mm
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
9. CONTACT MATERIAL: SILVER
- ▲ 10. 2011/65/EU (ROHS) COMPLIANT
- ▲ 11. PACKAGING: TAPE & REEL (600 PER REEL)
12. ▲ DENOTES CRITICAL PARAMETER

C	22677	ADD ACTUATOR COLOR BLACK NOTE	1/16/17	MW	 E-SWITCH®				
B	18199	REEL QTY WAS 1,100	8/5/08	BLR					
A	18189	RELEASED FOR PRODUCTION	7/28/08	BLR	TITLE TL3301BF160QJ				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 4:1	DATE 8/5/2008	DR BLR	DWG P010710	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3301BF160QJ](#)