




CIRCUIT: SPST





PCB LAYOUT



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: x.x =  $\pm 0.4$   
x.xx =  $\pm 0.25$
3. TERM. NOS. FOR REF ONLY
4. RATING: 50 MILLI-AMPS @24VDC
5. TRAVEL: 1.0 +/-0.5mm
6. CONTACT RESISTANCE: 30 MILLIOHMS MAX
7. INSULATION RESISTANCE: 10M OHMS MIN. AT 100VDC
8. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE
- ▲ 9. OPERATING FORCE: 300  $\pm$  75 GF
10. PACKAGING: TUBE, 45 PIECES PER TUBE
11. LIFE CYCLES: 10,000,000 ACTUATIONS
12. ▲ DENOTES CRITICAL PARAMETER
13. 2002/95/EC (ROHS) COMPLIANT



▲ BLACK ACTUATOR



TITLE TL6200DBF300QP

|     |        |             |          |    |
|-----|--------|-------------|----------|----|
| A   | 22054  | New Release | 11/25/15 | MW |
| REV | PCR NO | DESCRIPTION | DATE     | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|              |                    |          |                |          |
|--------------|--------------------|----------|----------------|----------|
| SCALE<br>2:1 | DATE<br>11/18/2015 | DR<br>MW | DWG<br>T060007 | REV<br>A |
|--------------|--------------------|----------|----------------|----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL6200DBF300QP](#)