









NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X= ± 0.4
X.XX= ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE 260 $\pm$ 70gf
6. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE.
7. TRAVEL: 0.15 $\pm$ 0.1mm
8. CONTACT RESISTANCE 100m Ω MAX. (INITIAL)
9. INSULATION RESISTANCE 100M Ω MIN. @500VDC
10. MECHANICAL/ELECTRICAL LIFE: 30,000 CYCLES
11. BOUNCE: 10msec MAX.
- ▲ 12. CONTACT MATERIAL: SILVER
- ▲ 13. MOISTURE PROTECTION: IP67
14. ▲ DENOTES CRITICAL PARAMETER
15. OPERATING TEMP: -40°C to 85°C
16. PACKAGING: TAPE AND REEL, 1,800 PCS/REEL



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100883	RELEASE	04/05/22	JS	TITLE TL6400AF260QJ				100121648
					SCALE	DATE	DR	DWG	REV
					8:1	3/29/2022	JS	P170002	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL6400AF260QJ](#)