






PANEL MOUNTING	
PANEL THICK	W
0.75 - 1.25	17.6 - 17.8
1.25 - 2.0	17.8 - 18.0
2.0 - 3.0	18.0 - 18.2



▲ **ILLUMINATION COLOR: RED/GREEN**



NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERM. NOS. FOR REFERENCE ONLY.
- CONTACT RATING: 0.5A @ 100VAC
0.2A @ 250VAC
0.5A @ 25VDC
- CONTACT MATERIAL: SILVER
- ELECTRICAL LIFE: 200,000 Typical
- MECHANICAL LIFE:
1,000,000 CYCLES TYP.
- CONTACT RESISTANCE:
50 MILLI OHM INITIAL TYP. MAX.
- DIELECTRIC STRENGTH:
1000 VAC FOR 1 MIN.
- TRAVEL TO MAKE: 2.20mm ± 0.2
- OPERATING FORCE: 200 +/- 100 gf
- OPERATING TEMPERATURE: -40° to +85°C
- ▲ DENOTES CRITICAL PARAMETER
- LED COLOR: RED: 3 CHIPS; 1.95-2.5 VDC @20mA TYP.
GRN: 3 CHIPS; 2.1-2.5 VDC @20mA TYP.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
I	ECO-101562	DIM 19.5+/-0.50 WAS 19.50	02/22/23	JS	TITLE ULP12OAM1QPMCL1REDGRN				000006906
					SCALE	DATE	DR	DWG	REV
					3:2	10/1/2009	BLR	B810030	I

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12OAM1QPMCL1REDGRN](#)