







PANEL MOUNTING	
PANEL THICK	W
0.75 - 1.25	17.6 - 17.8
1.25 - 2.0	17.8 - 18.0
2.0 - 3.0	18.0 - 18.2

PANEL MOUNTING

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATING: 0.1VA MAX. @ 28VDC
5. CONTACT MATERIAL: GOLD
6. ELECTRICAL LIFE: 200,000 TYP
7. MECHANICAL LIFE:
1,000,000 CYCLES TYP.
8. CONTACT RESISTANCE: 100 MILLI OHM MAX.
9. DIELECTRIC STRENGTH:
1000 VAC FOR 1 MIN.
10. TRAVEL TO MAKE: 2.20mm ±0.2
11. OPERATING FORCE: 200 +/- 100 gf
12. OPERATING TEMPERATURE: -40° to +85°C
13. ▲ DENOTES CRITICAL PARAMETER
- ▲ 14. LED COLOR: YEL: 3 CHIPS; 1.5-2.3 VDC @20mA TYP.
BLU: 1 CHIPS; 3.3-4.0 VDC @20mA TYP.

ILLUMINATION
COLOR: BLUE/YELLOW

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
H	ECO-101562	DIM 19.5+/- .50 WAS 19.50	02/22/23	JS	TITLE ULP12OAM1RPMCL1YELBLU				000006907
					SCALE	DATE	DR	DWG	REV
					3:2	10/1/2009	BLR	B810032	H

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12OAM1RPMCL1YELBLU](#)