






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = $\pm 0.4\text{mm}$
X.XX = $\pm 0.25\text{mm}$
3. RATING: DC 30V, 0.3A
4. OPERATING FORCE: $200 \pm 100\text{gf}$
5. TRAVEL: 3.3mm FULL TRAVEL
6. LIFE CYCLES: 10,000 CYCLES
7. OPERATING TEMPERATURE: -20°C to 70°C
8. CONTACT RESISTANCE: 20mW MAX.
9. INSULATION RESISTANCE: 100MW MIN@ 500VDC.
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2011/65/EU (RoHS) COMPLIANT.



▲ TRANSPARENT BUTTON
LED COLOR: GREEN



LED SPECS	UNITS	GREEN
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	2.1 TYP-2.5 MAX
LUMINOUS INTENSITY @ 20mA	mcd	400 TYP



E-SWITCH®

TITLE WBL4UOAGQR05CLR

SCALE

2:1

DATE

3/14/2017

DR

MW

DWG

B400017

REV

A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	22760	New Release	3/14/17	MW
REV	PCR NO	DESCRIPTION	DATE	BY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[WBL4UOAGQR05CLR](#)