









NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATINGS: 30mA @ 12VDC
5. CONTACTS: FIXED AND MOVING:
COPPER ALLOY W/GOLD PLATE
6. OPERATING FORCE: 150 ± 50 grams
7. OPERATING TRAVEL: 1.5MM ± 0.3MM
8. CONTINUOUS CURRENT RATING: 120mA
9. POWER RATING: 240mW
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT

LED SPECS	UNITS	BLUE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	3.5 TO 3.8
LUMINOUS INTENSITY	mcd	500 TYP.



TITLE 5511MBLKBLU

A	20403	RELEASE FOR PRODUCTION	1/18/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE
2:1DATE
1/18/2012DR
BGLDWG
XR0251PREV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

5511MBLKBLU