





RECOMMEND PANEL MOUNTING





▲ SPDT

CONTACT CONFIGURATION

## NOTES:


1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: 0.0±0.4  
0.00±0.25
3. TERM. NOS. FOR REF. ONLY.
4. RATING: 5A @250VAC  
8A @125VAC  
.2A @250VDC  
6A @24VDC
5. INSULATION: 1,000 MΩ MIN.
6. DIELECTRIC STRENGTH: 2000V FOR 1 MIN.
7. SEALED TO IP65.
8. TRAVEL: 3.0MM FULL TRAVEL, 2.0MM LATCH
9. ELECTRICAL LIFE: >50,000 CYCLES
10. OPERATING TEMP: -25C TO +55C
11. PANEL THICKNESS: 0.5MM TO 3.0MM
- ▲ 12. LAMP : BLUE LED ; 12 VDC
13. ▲ DENOTES CRITICAL PARAMETER.
14. PACKAGE: BOX/10 PER
15. 2002/95/EC (ROHS) COMPLIANT



## ▲ Parts List

| ITEM | QTY | PART NUMBER | DESCRIPTION                      |
|------|-----|-------------|----------------------------------|
| 1    | 1   | F060602     | LASEEV110                        |
| 2    | 1   | F060251     | 25MM BLUE LENS SUB-ASSY (OPAQUE) |
| 3    | 1   | F051705     | 30MM FLUSH MOUNT RETAINER        |
| 4    | 1   | F051704     | 30MM FLUSH MOUNT BEZEL           |
| 5    | 1   | F050432     | 5000432 LAMP - LED 12VDC BLUE    |

B



TITLE LASEEV31JBLUBLU

SCALE

DATE

12/10/2012

DR

EBP

DWG

XF0774P

REV

B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[LASEEV31JBLUBLU](#)