




RECOMMENDED P.C.B. LAYOUT



KNDB DETAIL



SCALE 4:1



SWITCH FUNCTION	
POS. 1	POS. 2
2-1,5-4	2-3,5-6

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 1A@ 30VDC
5. CONTACT RESISTANCE: 20mILLI-OHMS max.
6. INSULATION RESISTANCE: 500VDC 100Mega-OHMS min.
7. TRAVEL: 2.0mm
8. TIMING: SHORTING
9. OPERATING TEMP: -40° TO +85°



8. TIMING: SHORTING				
9. OPERATING TEMP: -40° TO +85°				
B	11944	ADDED NOTE 9	1/24/02	CJC
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
TITLE				
EG2263				
E-SWITCH®				
SCALE		DR		REV
2:1		CJC		B
DATE		DWG		
1/24/02		P122380		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[EG2263](#)